






Voltage rating:250V AC/DC
Current rating: 5A AC / DC
Withstanding voltage: 1000V AC/minute
Temperature range: -25°C~+85°C
Insulation resistance:≥1000MΩ
Contact resistance:≤10mΩ
After environmental testing:≤20mΩ

C3030 W R S-2*01 D-LP SW

- ① Series No.
- ② Category : W-WAFER
- ③ Welding Board Angle : R-Straight 180°
- ④ Welding Way : S-SMT
- ⑤ Row No.-Pin No. : 2xXX-2x02P-2x22P
- ⑥ Plug the Pin & Special No. : D-With Solder Tabs
- ⑦ Material: LP-LPC 94V-0
- ⑧ Plating Category: SN-Bright Tin Plating;
G05-Contact Gold 5u"
SW-Fog Tin plating
- ⑨ Color : Blank-Natural Color

Poles	Dimensions (mm)		Poles	Dimensions (mm)	
	AB			AB	
2*01	6.65	--	2*07	24.65	18.00
2*02	9.65	3.00	2*08	27.65	21.00
2*03	12.65	6.00	2*09	30.65	24.00
2*04	15.65	9.00	2*10	33.65	27.00
2*05	18.65	12.00	2*11	36.65	30.00
2*06	21.65	15.00	2*12	39.65	33.00

C3030WRS-2*01D-LPSW	LCP UL 94V-0	Brass	Matte tin	Brass	Tin-Plated	X3030 WRS
C3030WRS-2*01D-LPG05			Ni:50u"Min;Sn:120u"Min; Contact Area Gold:5u" Min.			
C3030WRS-2*01D-LPSN			Tin-Plated			
PART NO	Material	Material(Pin)	Finish(Pin)	Material (Solder Tabs)	Finish (Solder Tabs)	

						DSND		DATE		SCALE: N/A	MODEL TYPE: 3.00 mm Crimp Style Connectors		
Δ x					units: mm	DWN		DATE		VIEW: 	PART NO.: C3030WRS-2*01D-LPSW		
Δ x					X.X ± 0.2 mm	CHKD		DATE		UNIT: mm/in	DWG NO.: X-C3030WRS-2*01D-LPSW		
Δ x					X.XX ± 0.1 mm								
MARK	DESCRIPTION					APPD		DATE		SIZE: A4			
REVISIONS					UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT 1.0g	*SHEET 1/1
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn													