




RoSH


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.28	阿树



CIRCUIT DIAGRAM



REFERENCE DRAWING



P.C.B. LAYOUT

- Specifications (规格):
- 1.Voltage rating (额定电压): DC 12V
 - 2.Current rating (额定电流): 100mA AC/DC
 - 3.Withstanding voltage (耐压值): ≥250V AC/minute
 - 4.Insulation resistance (绝缘电阻): ≥100MΩ Min
 - 5.Contact resistance (接触电阻): ≤100mΩ Max
 - 6.Operating force (动作力): 160±50gf
 - 7.Travel (行程): 0.25+0.2/-0.10 mm
 - 8.Temperature range (使用温度): -20℃~+70℃

8.40mm	6.80mm	BLACK	BLACK	160±30gf	100,000 Cycles
"H"	"L"	STEM COLOR	CASE COLOR	O/FORCE	LIFE
DESIGN	阿树	VIEW:	UNIT: mm/in	MODEL TYPE:	TACT SWITCH
CHECKED		SIZE: A4	PART NO.:	TC-TL54-C	
APPROVED			DWG NO.:		

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE	PAGE	REVISION
N/A	1/1	A1