


A


B

C

D



电路简图



Specifications:

规格:

电气额定值Electrical Rating: 16A 250V AC

环境温度Ambient temperature:T125

电气寿命Electrical lifetime:5E4 cycles

动作力Operating force:5-1.5N

自由位置Free position:23.2±1.5mm

动作位置Operating position: 21.2±1.5mm

接触电阻Contact Resistance:≤50mΩ

耐压(Withstand Voltage): 端与端500V/60S/5mA,

端与壳1500V/60S/5mA.

绝缘电阻(Insulation Resistance): ≥100MΩ (Test Voltage 500VDC)


1转换型 SPDT	2常闭型 SPST-NC	3常开型 SPST-NO	AuGLAR	±5°
			X.	±0.40
			X.x	±0.30
			X.xx	±0.20
			X.xxx	±0.15
			UNSPECIFIED TOLERANCES	
www.helloxkb.com	www.helloxkb.cn	www.xk-dg.cn		



XKB INDUSTRIAL PRECISION CO.,LIMITED

REVISIONS

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		尺寸修正, 图面升级整理图面	2024.8.2	阿树
A2	N/A		图面修正, 图面升级整理图面	2024.12.2	阿树



DESIGN	阿树	VIEW:	MODEL TYPE: MICRO SWITCH
CHECKED		UNIT: mm/in	PART NO.: DV-16-246UN-3
APPROVED		SIZE: A4	DWG NO.:
			SCALE: N/A
			PAGE: 1/1
			REVISION: A1