







| REVISIONS |         |          |                 |            |        |
|-----------|---------|----------|-----------------|------------|--------|
| REV.      | ECN NO. | LOCATION | DESCRIPTION     | DATE       | DESIGN |
| A0        | N/A     |          | INITIAL RELEASE | /          | /      |
| A1        | N/A     |          | 图面升级整理图面        | 2025.06.16 | 阿树     |



SK12D07L4B

| L(mm) | Colour  |
|-------|---------|
| 2~12  | B:Black |
|       | R:Red   |



|                        |             |
|------------------------|-------------|
| RATING                 | 0.3A 50V DC |
| CIRCUIT                | 1P2T        |
| CONTACT RESISTANCE     | 100mΩ MAX   |
| TRAVEL                 | 2mm         |
| OPERATING FORCE        | 250±100gf   |
| OPERATING LIFE(CYCLES) | 10,000      |

|      |           |     |                |           |
|------|-----------|-----|----------------|-----------|
| 4    | Terminal  | 3   | Brass(0.30t)   | ag Plated |
| 3    | Base      | 1   | Phenolic Resin |           |
| 2    | Cover     | 1   | Sus            | Natural   |
| 1    | Keystake  | 1   | PA66           | Black     |
| ITEM | PAPT NAME | QTY | MATERIAL       | FINISHING |

|                        |       |
|------------------------|-------|
| AuGLAR                 | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERAUCES |       |



DESIGN  
CHECKED  
APPROVED

阿树

VIEW:   
UNIT: mm/in  
SIZE: A4

MODEL TYPE:  
SLIDE SWITCH  
PART NO.:  
SK12D07L4B  
DWG NO.:  
X-SK12D07L4B

XKB INDUSTRIAL PRECISION CO.,LIMITED

|       |      |          |
|-------|------|----------|
| SCALE | PAGE | REVISION |
| N/A   | 1/1  | A1       |