

HSF



RoHS




SPECIFICATION

Current Rating: 1Amp
 Insulation Resistance: 1000MΩ min
 Contact Resistance: 20MΩ max
 Withstand Voltage: 500V AC/DC
 Operating Temperature: -40°C to +105°C
 Contact Material: Brass
 Contact Plating: Au or Sn Over Ni
 Insulator Material: PA6T+30%GF UL 94V-0

Ordering Code:

BHAS01 - X - X - X - X - X
 ① ② ③ ④ ⑤ ⑥

- ① Series No:
 ② No. of Contacts
 06 08 10 14 16
 20 24 26 30 32
 34 40 44 50 60
 64 80 100
 ③ Contact Plating:
 G0:Gold flash S0:Selective
 G1:3U" Gold S1:Selective 3u"
 G2:5u" Gold S2:Selective 5u"
 G3:10u" Gold S3:Selective 10u"
 G4:15u" Gold S4:Selective 15u"
 G5:30u" Gold S5:Selective 30u"
 SN: Tin
 ④ Color Insulator
 B:Black
 U:Blue
 W:White
 ⑤ Insulator Material
 B:PA6T
 C:LCP
 E:PA9T
 ⑥ Packing
 A:Tray
 B:Bag
 T:Tube
 U:Tube+CAP
 R:Tape&Reel
 W:Tape&Reel+CAP



SECTION A-A

Recommended P.C.B Layout(Top Side)

(PCB BOARD TOLERANCE ± 0.05)

Unless Otherwise specified tolerance
 X. ± 0.35 X.XX: ± 0.20
 X.X: ± 0.25 X.XXX: ± 0.15

SCALE: As Shown UNIT: mm
 DRAW: YG ZHONG DATE: 01/05/2016
 CHECK: BobYang DATE: 01/05/2016



3rd ANGLE PROJECTION

Antenk ANTENK ELECTRONICS CO., LTD
 Http://www.antenk.com
 E-mail:sales@antenk.com

TITLE:

1.27mm Box Header 180° H=4.90

DRAWING NO: BHAS01-X-X-X-X-X

PRODUCT NO: BHAS01-X-X-X-X-X

REV

DESCRIPTION

DATE

1

2

3

4

5

6

7

8