


① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category : H-HSG
- ③ Welging Board Angle : F-Female HSG
- ④ Row No.-Pin no.: XX-02P~12P
- ⑤ Plug the Pin & special No. : I-Without Ears
G-With Ears
- ⑥ Material : N2-PA66 94 V-2;
- ⑦ Color: Blank -Natural Color ; WH-White

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	3.00	6.90	08	21.00	24.90
03	6.00	9.90	09	24.00	27.90
04	9.00	12.90	10	27.00	30.90
05	12.00	15.90	11	30.00	33.90
06	15.00	18.90	12	33.00	36.90
07	18.00	21.90			

X3025HF-05G-N2	Nylon 66 94V-2	Natural Color	X3025TM	X3025HM	With Ears
X3025HF-05G-N2WH	Nylon 66 94V-2	White			
X3025HF-05L-N2	Nylon 66 94V-2	Natural Color	X3025TM	X3025HM	Without Ears
X3025HF-05L-N2	Nylon 66 94V-2	White			
PART NO	Material	Color	Suitable XKB Terminal	Material With XKB Housing	Note

				XKB	ANGLAR	±5°
Δ x					L ≤ 4	±0.2
Δ x					4 < L ≤ 16	±0.3
Δ x					16 < L ≤ 63	±0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com						

DSND		DATE		SCALE: N/A	MODEL TYPE:		
DWN		DATE		VIEW: 	3.00 mm Crimp Style Connectors		
CHKD		DATE		UNIT: mm/in	PART NO.: X3025HF-05I-N2		
APPD		DATE		SIZE: A4	DWG NO.: X-X3025HF-05I-N2		
XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT	SHEET	REVISION
					1.0g	1/1	A0