


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A	(A1)X3	产品尺寸变更, 图面升级整理图面	2025.06.19	阿树








- SPECIFICATIONS
- Voltage rating:100V AC/DC
 - Current rating:2A AC/DC
 - Withstanding Voltage:800V AC/minute
 - Temperature range:-40°C~+125°C
 - Insulation resistance:≥1000MΩ
 - Contact resistance:≤10mΩ
 - After environmental testing:≤20mΩ

PART NO.:

X2016 W V S-07-9T SW
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Category:W-Wafer
③Welding Board Angle:V-Sright 180°
④Welding Way:S-SMT
⑤Row No.Pin No:XX-02~20Pin
⑥Material:9T-PA9T 94V-0
⑦Plating:SW-MatteTin Plating;

Poles	Dimensions/mm	
	A	B
02	2.00	8.00
03	4.00	10.00
04	6.00	12.00
05	8.00	14.00
06	10.00	16.00
07	12.00	18.00
08	14.00	20.00
09	16.00	22.00
10	18.00	24.00
11	20.00	26.00
12	22.00	28.00
13	24.00	30.00
14	26.00	32.00
15	28.00	34.00
16	30.00	36.00



X2016WVS-07-9TSW	PA9T UL 94V-0	Brass	Tin-Plated	X2016H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Terminal
DESIGN	阿树	VIEW:	MODEL TYPE: 2.00mm Crimp Style Connectors	
CHECKED		UNIT: mm/in	PART NO.: X2016WVS-07-9TSW	
APPROVED		SIZE: A4	DWG NO.: X-X2016WVS-07-9TSW	
SCALE			PAGE	REVISION
N/A			1/2	A1

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED