





1

2

3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A	①X2	产品尺寸变更, 图面升级整理图面	2025.05.24	阿树




Specifications:
规格:
Voltage rating:600V AC/DC
额定电压: 600V AC/DC
Current rating:7A AC/DC
额定电流: 7A AC/DC
Withstanding voltage:1500V AC/minute
耐受电压: 1500V AC/分钟
Temperature range:-25℃~+85℃
温度范围: -25℃~+85℃
Insulation resistance:1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:20mΩ Max
接触电阻: 20mΩ Max

PART NO.:

X9357 H E-2x07 B-N0 XX
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
- ②Category:H-HSG
- ③Welding Board Angle:F-Fmale HGS
- ④Row No.-Pin No.:2xXX-2x04P~2x22P
- ⑤Plug the Pin & special No.: B-With a trough
- ⑥Material:N0-PA66 94V-0
- ⑦Color:Blank-natural color

Poles	Dimensions(mm)			
	A	B	C	D
2x02	15.80	4.20	19.80	16.30
2x03	20.00	8.40	24.00	20.50
2x04	24.20	12.60	28.20	24.70
2x05	28.40	16.80	32.40	28.90
2x06	32.60	21.00	36.60	33.10
2x07	36.80	25.20	40.80	37.30
2x08	41.00	29.40	45.00	41.50
2x09	45.20	33.60	49.20	45.70
2x10	49.40	37.80	53.40	49.90
2x11	53.60	42.00	57.60	54.10
2x12	57.80	46.20	61.80	58.30



RECOMMENDED PCB CUTOUT

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE: 4.20mm Crimp Style Connectors
CHECKED		UNIT:	mm/in	PART NO.: X9357HF-2x07B-N0
APPROVED		SIZE:	A4	DWG NO.: X-X9357HF-2x07B-N0