









Specifications:

- 1.Voltage rating: 300V AC/ DC
- 2.Current rating: 1A AC/DC
- 3.Withstanding voltage: 900V AC/minute
- 4.Temperature range: -25° ~+85
- 5.Insulation resistance: ≥100MΩ
- 6.Contact resistance: 20mΩ Max
- 7.Material:PA9T UL94V-0
PIN Brass Tin-plated

X6200 W F-02-9T SN

① ②③ ④ ⑤ ⑥

- ① Series No
- ② Category: W-WAFER
- ③ Welding Board Angle: F-Female
- ④ Row No.-Pin No.: XX-Single Row
- ⑤ Material: 9T-PA9T UL94V-0
- ⑥ Plating Category: SN- Tin Plating



Mating Condition

Bottom Chassis

X6200WF-02-9TSN	PA9T	Brass	Tin-Plating	X6200WM
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Wafer
		DSND	SCALE: N/A	MODEL TYPE: 6.2mm BTB Style Connectors
		DWN	VIEW:	PART NO.: X6200WF-02-9TSN
		CHKD	UNIT: mm/in	DWG NO.: X-X6200WF-02-9TSN
		APPD	SIZE: A4	WEIGHT
		XKB INDUSTRIAL PRECISION CO.,LIMITED		SHEET 1/1
				REVISION A0

广东星坤科技股份有限公司

生
效

日期

文件工程章

REVISIONS

DATE

REVISED

APPROVED

ANGULAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn