

Specifications:

规格:

Voltage rating:30V AC/DC

额定电压: 30V AC/DC

Current rating: 0.5A AC/DC

额定电流: 0.5A AC/DC

Withstanding voltage:200V AC/minute

耐压电压: 200V AC/分钟

Temperature range: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$

温度范围: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$



Insulation resistance: $\geq 100\text{M}\Omega$

绝缘电阻: $\geq 100\text{M}\Omega$

Contact resistance: $\leq 20\text{m}\Omega$

接触电阻: $\leq 20\text{m}\Omega$

After environment



PART NO.:

X0800 W R S - 03 HF- LP V01

① ② ③ ④ ⑤ ⑥ ⑦ ⑧

①Series No.

②Category: W-wafer

③Welding Board Angle: R-90°

④Welding Way:S-SMT


⑤Row No.—Pin No.XX—Single

⑥ Plug the Pin & Special NO.:HF-Halogen free

⑦Material: LP-LCP 94V-0

⑧Planting Category : V01:All Gold-Flash;

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	0.80	1.90	3.78	11	8.00	9.10	10.98
03	1.60	2.70	4.58	12	8.80	9.90	11.78
04	2.40	3.50	5.38	13	9.60	10.70	12.58
05	3.20	4.30	6.18	14	10.40	11.50	13.38
06	4.00	5.10	6.98	15	11.20	12.30	14.18
07	4.80	5.90	7.78	16	12.00	13.10	14.98
08	5.60	6.70	8.58	17	12.80	13.90	15.78
09	6.40	7.50	9.38	18	13.60	14.70	16.58
10	7.20	8.30	10.18	19	14.40	15.50	17.38



P.C.B Layout

X0800WRS-03HF-LPV01	LCP UL 94V-0 Halogen-free	Phosphor Bronze	Tin-Plated	Brass	Tin-Plated	X0800H
PART NO	Material	Material(Pin)	Finish(pin)	Material (Solder Tabs)	Finish (Solder Tabs)	Suitable XKB Housing

ANGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	

XK13 星城 Connection

DESIGN	阿树	VIEW:		MODEL TYPE: 0.80mm IDC Style Connectors						
CHECKED		UNIT: mm/in		PART NO.: X0800WRS-03HF-LPV01						
APPROVED		SIZE: A4		DWG NO.: X-X0800WRS-03HF-LPV01						
PRECISION CO.,LIMITED				<table><tr><td>SCALE</td><td>PAGE</td><td>REVISION</td></tr><tr><td>N/A</td><td>1 / 1</td><td>A1</td></tr></table>	SCALE	PAGE	REVISION	N/A	1 / 1	A1
SCALE	PAGE	REVISION								
N/A	1 / 1	A1								