

1

2

3

4

## REVISIONS

| REV. | ECN NO. | LOCATION | DESCRIPTION     | DATE       | DESIGN |
|------|---------|----------|-----------------|------------|--------|
| A0   | N/A     |          | INITIAL RELEASE | /          | /      |
| A1   | N/A     |          | 图面升级整理图面        | 2025.05.22 | 阿树     |

## Specifications:

## 规格:

Current rating:3A AC/DC

额定电流: 3A AC/DC

Voltage rating:250V AC

额定电压: 250V AC

Withstanding voltage:500V AC/MIN

耐受电压: ≥500V AC/分钟

Temperature range:-55℃~+105℃

温度范围: -55℃~+105℃

Insulation resistance:1000MΩMIN

绝缘电阻: ≥1000MΩ

Contact resistance:30mΩMAN

接触电阻:≤30mΩ

Material And FINISHED:

材料和成本:

INSULATOR:PBT UL 94V-0

绝缘体: PBT UL 94V-0

SHELL: SPCC-SD Plated Ni / Au / Sn

外壳: 铁合金 镀镍/金/锡

CONTACT MATERIAL:COPPER ALLOY

触点材料: 铜合金

PART NO.:

X03 15 F T 17 B2 H  
① ② ③ ④ ⑤ ⑥ ⑦

①Series NO.

②Row No.Pin No.XX-09;15;25;37

③Welding Board Angle :F-Female





④T: Tradutional

⑤Planting Category: 1:1U' 2:2U' 3:3U' 4:5U' 5:15U' 6:30U' 7:AuSn

⑥Color:B:Black W:White BL:Blue Y:Yellow G:Green R:Red

⑦1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4; 6:TYPE-6

| NO.OF CONTACT | A     | B     | C     |
|---------------|-------|-------|-------|
| 09            | 30.80 | 24.99 | 16.35 |
| 15            | 39.20 | 33.30 | 24.75 |
| 25            | 53.05 | 47.04 | 38.35 |
| 37            | 69.40 | 63.50 | 54.75 |

| 铆合方式 | TYPE-1:铆合                                                                             | TYPE-6:直铆锁                                                                            | TYPE-3:叉锁                                                                             | TYPE-2:铆合锁螺丝                                                                          |
|------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| 图式   |  |  |  |  |

|                        |       |
|------------------------|-------|
| AuGLAR                 | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERANCES |       |

**XKLB** 星城  
Connection

|          |    |                                                                                             |                         |
|----------|----|---------------------------------------------------------------------------------------------|-------------------------|
| DESIGN   | 阿树 | VIEW:  | MODEL TYPE: D-SUB       |
| CHECKED  |    | UNIT: mm/in                                                                                 | PART NO.: X0315FT17B2H  |
| APPROVED |    | SIZE: A4                                                                                    | DWG NO.: X-X0315FT17B2H |

| SCALE | PAGE | REVISION |
|-------|------|----------|
| N/A   | 1/1  | A1       |

1

2

3

4