

1

2


3

4


REVISIONS

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.9.12	阿树


A






B



C



D



■ SPECIFICATIONS

- Voltage rating: 250V AC/DC
- Current rating: 3A AC/DC
- Withstanding Voltage: 1000V AC/minute
- Temperature range: -40°C ~ +125°C
- Insulation resistance: ≥ 1000MΩ
- Contact resistance: ≤ 10mΩ

PART NO.:

X2508 W V S-03-9T SW
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No
② Category: W—Wafer
③ Welding Board Angle: V—Stright 180°
④ Welding Way: S—SMT
⑤ Row No. Pin No: XX-02~15Pin
⑥ Material: 9T—PA9T 94V-0
⑦ Planting: SW—Matte Tin Plating

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	10.00	5.30	09	16.00	24.00	6.40
03	4.00	12.00		10	18.00	26.00	
04	6.00	14.00		11	20.00	28.00	
05	8.00	16.00	6.40	12	22.00	30.00	
06	10.00	18.00		13	24.00	32.00	
07	12.00	20.00		14	26.00	34.00	
08	14.00	22.00		15	28.00	36.00	

X2508WVS-03-9TSW	PA9T	Barss	X2508H
PART NO	Material	Material(Pin)	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	2.50mm Crimp Style Connectors
CHECKED		UNIT:	mm/in	PART NO.:	X2508WVS-03-9TSW
APPROVED		SIZE:	A4	DWG NO.:	X-X2508WVS-03-9TSW
		SCALE	N/A	PAGE	1/1
				REVISION	A1

1

2

3

4