







Specifications:
规格:
Voltage rating:100V AC/DC
额定电压: 100V AC/DC
Current rating:1A AC/DC
额定电流: 1A AC/DC
Withstanding voltage:500V AC/minute
耐受电压: 500V AC/分钟
Temperature range:-40℃~+85℃
温度范围: -40℃~+85℃
Insulation resistance:500MΩ min
绝缘电阻: 500MΩ Min
Contact resistance:20mΩ Max
接触电阻: 20mΩ Max

X1502 H - 09 - N0
① ② ③ ④

- 1.Series No
- 2.Category:H-Housing
- 3.Row No.Pin No:XX-02~15 Pin
- 4.Material:N0-PA66 UL94V-0



Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	1.50	4.50	09	12.00	15.00
03	3.00	6.00	10	13.50	16.50
04	4.50	7.50	11	15.00	18.00
05	6.00	9.00	12	16.50	19.50
06	7.50	10.50	13	18.00	21.00
07	9.00	12.00	14	19.50	22.50
08	10.50	13.50	15	21.00	24.00

X1502H-09-N0	PA66	X1502W	X1502T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

DSND		SCALE: N/A	MODEL TYPE: 1.5mm Crimp Style Connector
DWN		VIEW:	PART NO.: X1502H-09-N0
CHKD		UNIT: mm/in	DWG NO.: X-X1502H-09-N0
APPD		SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT
			SHEET
			REVISION
			1/1
			A0

					ANGULAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						