

Technical Data
Pin(outer sleeve):Brass,machined CuZn38pb2
Clp (Contact 6 Finger):Beryllium copper,heat teated
Insulator:PPS UL94V-0 colour:black
Current rating:3Amps
Mating Pinø:0.635/0.889mm
Forces:(polished steel gaugeø0.66mm)
-Insertion:1.2N typ
-Withdrawal:0.6N typ
Mechanical Life:min 500 cycles
Contact resistance: 10mΩ max
Dielectric strength:1000V
Operating temperature:-40 °C to +105°C
Soldering temperature:+255°C

X5511 F V-05-C70 D30-1000

① ② ③ ④ ⑤ ⑥ ⑦

- | | | | | | | |
|---|--|----------------------------------|---------------|---|---|--------------|
| X5511FV-05-C70D30-1000 | | PPS 94V-0 | Brass | Tin Gold 1u" | X5511F | |
| PART NO | | Material | Material(Pin) | Finish(Terminal) | Mates With XKB
Pin Header | |
|  | | DESIGN | 阿树 | VIEW:  | MODEL TYPE:
2.54mm BTB Style Connector | |
| | | CHECKED | | UNIT: mm/in | PART NO.:
X5511FV-05-C70D30-1000 | |
| | | APPROVED | | SIZE: A4 | DWG NO.:
X-X5511FV-05-C70D30-1000 | |
| | | INDUSTRIAL PRECISION CO.,LIMITED | | | | SCALE
N/A |

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	

XK13 星城
Connection

XKB INDUSTRIAL PRECISION CO.,LIMITED

www.helloxkb.com	www.helloxkb.cn	www.xk-dg.cn
------------------	-----------------	--------------