








Specifications:
规格:
Voltage rating:30V AC/DC
额定电压: 30V AC/DC
Current rating: 0.5A AC/DC
额定电流: 0.5A AC/DC
Withstanding voltage:200V AC/minute
耐压电压: 200V AC/分钟
Temperature range:-25℃~+85℃
温度范围: -25℃~+85℃
Insulation resistance:≥100MΩ
绝缘电阻: ≥100MΩ
Contact resistance: ≤20mΩ
接触电阻: ≤20mΩ
After environment testing: ≤40mΩ
环境试验后: ≤40mΩ

X800 W V S - 09 HF- LP V 01

① ②③④ ⑤ ⑥ ⑦ ⑧ ⑨

①Series No.

②Category: W-wafer

③Welding Board Angle: V-180°

④Welding Way:S-SMT

⑤Row No.-Pin No.XX-Single row

⑥Plug the Pin & Special NO.:HF-Halogen free


⑦Material: LP-LCP 94V-0

⑧Planting Category : V01:All Gold-Flash;

SN-Bright tin plating


⑨Color: Blank-natural color; BK-black

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
2	0.80	1.90	3.78	12	8.80	9.90	11.78
3	1.60	2.70	4.58	13	9.60	10.70	12.58
4	2.40	3.50	5.38	14	10.40	11.50	13.38
5	3.20	4.30	6.18	15	11.20	12.30	14.18
6	4.00	5.10	6.98	16	12.00	13.10	14.98
7	4.80	5.90	7.78	17	12.80	13.90	15.78
8	5.60	6.70	8.58	18	13.60	14.70	16.58
9	6.40	7.50	9.38	19	14.40	15.50	17.38
10	7.20	8.30	10.18	20	15.20	16.30	18.18
11	8.00	9.10	10.98				



Recommended P.C.B Layout

General Tolerance±0.05



X0800WVS-09HF-LPV01BK	PA6T UL 94V-0 Black (Halogen-free)	Phosphor Bronze	Gold-Flash	Brass	Gold-Flash	X0800T
X0800WVS-09HF-LPSNBK	PA6T UL 94V-0 (Halogen-free)		Gold-Flash		Gold-Flash	
X0800WVS-09HF-LPSN	LCP UL 94V-0 Halogen-free		Gold-Flash		Gold-Flash	
X0800WVS-09HF-LPV01			Tin-Plated		Tin-Plated	
PART NO	Material	Material(Pin)	Finish(pin)	Material (Solder Tabs)	Finish (Solder Tabs)	Suitable XKB Terminal

ΔX	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					
ΔX					
ΔX					
MARK					
REVISIONS					UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND	SCALE: N/A	MODEL TYPE: 0.8mm Crimp Style Connector
DWN	VIEW:	PART NO.: X0800WVS-09HF-LPV01
CHKD	UNIT: mm/in	DWG NO.: X-X0800WVS-09HF-LPV01
APPD	SIZE: A4	WEIGHT
		SHEET
		REVISION
		1/1
		A0