

1

2

3


4

A


B

C

D







Circuit diagram




P.C.B. LAYOUT


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.23	阿树




117




135




150




180




12U




16U




115G



151U






141U



000

DMX-XXXP-X

1:1A以下
3:3A

1:转换型 SPDT		2:常闭型 SPST-NC		3:常开型 SPST-NO	
					
					
AuGLAR	±5°				
X.	±0.40				
X.x	±0.30				
X.xx	±0.20				
X.xxx	±0.15				
UNSPECIFIED TOLERANCES					



DESIGN	阿树	VIEW:		MODEL TYPE:	MICRO SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	DM1-117P-1
APPROVED		SIZE:	A4	DWG NO.:	X-DM1-117P-1
		SCALE	N/A	PAGE	1/1
		REVISION	A1		

1

2

3

4