


Specifications:

规格:

Voltage rating:150V AC/DC

额定电压: 150V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:500V AC/minute

耐受电压: 500V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

After environmental testing:≤40mΩ

环境测试后: ≤40兆欧

X1503 H-03-N0

① ② ③ ④

- 1.Series No.
- 2.Category:H-HSG
- 3.Row No-Pin No: XX-04P~12P
- 4.Material :N0-PA66 94V-0

Poles	Dimensions(mm)			
	A	B	C	D
02		6.95	5.95	5.55
03	3.00	8.45	7.45	7.05
04	4.50	9.95	8.95	8.55
05	6.00	11.45	10.45	10.05
06	7.50	12.95	11.95	11.55
07	9.00	14.45	13.45	13.05
08	10.50	15.95	14.95	14.55
09	12.00	17.45	16.45	16.05
10	13.50	18.95	17.95	17.55
11	15.00	20.45	19.45	19.05
12	16.50	21.95	20.95	20.55

X1503H-03-N0	PA66 UL 94V-0	X1503T	X1503W
PART NO	Material	Suitable Terminal	Suitable XKB

Wire to board connector

						DSND		DATE		SCALE: N/A	MODEL TYPE: 1.50mm Crimp Style Connectors
ΔX					units: mm	DWN		DATE		VIEW:	PART NO.: X1503H-03-N0
ΔX					tolerance: X.X ±0.2mm	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X1503H-03-N0
ΔX					X.XX ±0.1mm	APPD		DATE		SIZE: A4	
MARK					X.XXX ±0.05mm						
REVISIONS						UNSPECIFIED TOLERANCES					
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn						XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT 1.0g
											SHEET 1/1
											REVISION A0