

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.06.05	阿树

A

B

C





D

A


B

C

D




P.C.B WELDING DRAWING



SPECIFICATION
Contact Rating: 50mA,12V DC
Contact Resistance: 100mΩ max
Insulation Resistance: 100MΩ min.500V DC
Dielectric Strength: 250V AC/1minute
Travel: 0.2mm
Operating Temp: -30℃~+85℃
Storage Temp: -30℃~+80℃


PAPT NO	TS-1177-C-B-B
Operating Force	B:160gf C:260gf
Height	H:A:1.5 B:2.0
Color	B:black W:white



CIRCUIT DIAGRAM

F	Button	LCP	1	Black
E	Panels	SUS	1	
D	Stuff	PI	1	Orange yellow
C	Shrapnel	SUS	2	Silver
B	Noumenon	LCP	1	Black
A	Card	Brass	1	Silver
ITEM	DESCRIPTION	MATERIAL	QTY	FINSH/COLOR

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: TACT SWITCH	
CHECKED		UNIT: mm/in	PART NO.: TS-1177-C-B-B	
APPROVED		SIZE: A4	DWG NO.: TS-1177-C-B-B	
			SCALE	PAGE
			N/A	1/1
			REVISION	
			A1	