

Specifications:
规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:1A AC/DC
额定电流: 1A AC/DC
Withstanding voltage:500V AC/minute
耐受电压: 500V AC/分钟
Temperature range:-40℃--+105℃
温度范围: -40℃--+105℃
Insulation resistance: 1000MΩ min
绝缘电阻: 1000MΩ Min
Contact resistance:20mΩ Max
接触电阻: 20mΩ Max

X2001 W V - 2x17 A - 6T V01
① ② ③ ④ ⑤ ⑥ ⑦
1.Series No
2.Category:W-Wafer
3.Welding Board Angle:V-Stright 180°
4.Row No.Pin No: 2xXX-2x03-2x30P
5.Category:A-No gap
6.Material:6T-Nylon 6T UL94V-0
7.Plating:V01-Gold Flash





Poles	Dimensions		Poles	Dimensions	
	A	B		A	B
2x03	4.00	13.30	2x12	22.00	31.30
2x04	6.00	15.30	2x13	24.00	33.30
2x05	8.00	17.30	2x15	28.00	37.30
2x06	10.00	19.30	2x17	32.00	41.30
2x07	12.00	21.30	2x18	34.00	43.30
2x08	14.00	23.30	2x20	38.00	47.30
2x09	16.00	25.30	2x22	42.00	51.30
2x10	18.00	27.30	2x25	48.00	57.30
2x11	20.00	29.30	2x30	58.00	67.30

X2001WV-2x17A-6TV01	Nylon 6T	Brass	X2001HA-2x17
			X2001HA2-2x17
PART N0	Material	Material(Pin)	Suitable XKB IDC

DSND		SCALE: N/A	MODEL TYPE: 2.0mm Jane cattle 简牛		
DWN		VIEW: 	PART NO.: X2001WV-2x17A-6TV01		
CHKD		UNIT: mm/in	DWG NO.: X-X2001WV-2x17A-6TV01		
APPD		SIZE: A4	WEIGHT	SHEET	REVISION
				1/1	A0

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED



P . C . B LAYOUT

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						