







Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:4A AC/DC

额定电流: 4A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-40℃~+105℃





温度范围: -40℃~+105℃

Insulation resistance:1000MΩ min


绝缘电阻: 1000MΩ Min

Contact resistance:30mΩ Max


接触电阻: 30mΩ Max




2x02 Pin




2x03 Pin




2x04 Pin




2x05 Pin



2x06 Pin



2x07 Pin



2x08 Pin

X2513 H - 2x03 A - 46
① ② ③ ④ ⑤

1.Series No

2.Category:H-HSG

3.Row No.Pin No:2xXX-2x02~2x12 Pin

4.Special No: A:Key A (Black)

B:Key B (Natural)

5.Material:46-Nylon 46+30%G.F UL94V-0

Poles	Dimensions(mm)
	A
2x02	7.70
2x03	10.20
2x04	12.70
2x05	15.20
2x06	17.70
2x07	20.20
2x08	22.70
2x12	32.70

X2513H-2x03A-46	Nylon 46+30%G.F	X2513W	X2513T
X2513H-2x03B-46			
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

DSND	SCALE: N/A	MODEL TYPE: 2.5mm Crimp Style Connector
DWN	VIEW:	
CHKD	UNIT: mm/in	PART NO.: X2513H-2x03A-46
APPD	SIZE: A4	DWG NO.: X-X2513H-2x03A-46

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5

REVISIONS					UNSPECIFIED TOLERANCES	

www.helloxkb.com www.helloxkb.cn www.xk-dg.cn

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
	1/1	A0