

1

2

3

4

A

B

C






D

A

B

C

D



ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	


规格 Specification:

- 额定值 Rating:3A 125/250VAC
- 接触电阻 Contact resistance:≤30 mΩ
- 绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)
- 电气寿命 Electronics life:>10000 cycles
- 操作力 Operation force:500±200gf
- 所有材料符合Rohs要求 All materials are Rohs compliant

PART NO.:

SS-X 03 22 S G-14 R 2 B B
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

- SS: XKB Vertical handle;
- Enclosure Material:
A-Metal case;
BLANK-Plastic case;
- Current Rating: 03-3A;
- Switch Circuit:22-2P2T;
- S: Wire bonding;
- Handle Shape: G-Camber handle;
- Handle Height: 3~15mm;
- Enclosure Shape:R-Locking rings enclosure;
- Terminal specs:
1:TYPE-1; 2:TYPE-2; 3:TYPE-3;
4:TYPE-4; 5:TYPE-5;
- Handle Colour:
B-Black; W-White; R-Red
- Housing Colour:
B-Black; W-White; R-Red



XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	桑 葚	VIEW:	MODEL TYPE: SLIDE SWITCH
CHECKED		UNIT: mm/in	PART NO.: SS-A0322SG-14R2BB
APPROVED		SIZE: A4	DWG NO.: X-SS-A0322SG-14R2BB
		SCALE	PAGE
		N/A	1/1
		REVISION	A0

1

2

3

4