

1

2

3

4

A

B

C







D

A

B

C

D



Remarks:  
1.Rated current, Voltage:DC 12V 50mA  
2.Contact resistance: ≤50 mΩ  
3.Insulation resistance: ≥100 mΩ  
4.The intensity of operations: 160 ±50gf  
5.Life requirements: 10000 times  
6.Withstand voltage: AC250V 1 minute  
7.All materials comply with RoHS2.0 standards

|                 |                         |
|-----------------|-------------------------|
| PAPT NO         | TS-1109S-B-F            |
| Operating Force | A:100gf B:160gf C:260gf |
| Height          | Code-x                  |

|      |           |          |     |               |
|------|-----------|----------|-----|---------------|
| ⑤    | Terminal  | Brass    | 4   | Ag Plating    |
| ④    | Housing   | PPA      | 1   | Black         |
| ③    | Shrapnel  | Sus      | 1   | Ag Plating    |
| ②    | Cover     | Brass    | 1   | Cu-Sn Plating |
| ①    | Button    | PPA      | 1   | Black         |
| ITEM | PAPT NAMF | MATERIAL | QTY | FINISHING     |

|                        |       |
|------------------------|-------|
| AuGLAR                 | ±5°   |
| X.                     | ±0.40 |
| X.x                    | ±0.30 |
| X.xx                   | ±0.20 |
| X.xxx                  | ±0.15 |
| UNSPECIFIED TOLERANCES |       |



|          |      |             |                        |
|----------|------|-------------|------------------------|
| DESIGN   | 阿树   | VIEW:       | MODEL TYPE:            |
| CHECKED  |      | UNIT: mm/in | TACT SWITCH            |
| APPROVED |      | SIZE: A4    | PART NO.: TS-1109S-B-F |
|          |      |             | DWG NO.: TS-1109S-B-F  |
| SCALE    | PAGE | REVISION    |                        |
| N/A      | 1/1  | A1          |                        |

1

2

3

4