



PCB LAYOUT

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-40℃-+105℃

温度范围: -40℃-+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

Material:PA6T UL94V-0

材质: PA6T UL94V-0

Plating Category:1U"Gold

镀层: 1U"Gold

Wave soldering temperature:255±5℃, 10S

波峰焊温度: 255±5℃, 10S

X6511 W V - 07 H - C60 D30  
① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:V-Stright 180°
- 4.Row No.Pin No:XX-02~40P
- 5.Plastic Height:H=2.5mm
- 6.Pin Length:C=6.0mm
- 7.Pin Length:D=3.0mm

|                    |          |               |                        |
|--------------------|----------|---------------|------------------------|
| X6511WV-07H-C60D30 | PA6T     | Brass         | X6511F                 |
| PART NO            | Material | Material(Pin) | Suitable XKB<br>Female |

| MARK                                          | DESCRIPTION | DATE | REVISED | APPROVED | UNSPECIFIED TOLERANCES |
|-----------------------------------------------|-------------|------|---------|----------|------------------------|
| ΔX                                            |             |      |         |          | ANGLAR ±5°             |
| ΔX                                            |             |      |         |          | L≤ 4 ±0.2              |
| ΔX                                            |             |      |         |          | 4<L≤ 16 ±0.3           |
| ΔX                                            |             |      |         |          | 16<L≤ 63 ±0.4          |
| ΔX                                            |             |      |         |          | L> 63 ±0.5             |
| REVISIONS                                     |             |      |         |          |                        |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn |             |      |         |          |                        |

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

|                       |  |                                                                                             |                                     |       |          |
|-----------------------|--|---------------------------------------------------------------------------------------------|-------------------------------------|-------|----------|
| DSND                  |  | SCALE: N/A                                                                                  | MODEL TYPE:<br>2.54mm BTB Connector |       |          |
| DWN                   |  | VIEW:  | PART NO.:<br>X6511WV-07H-C60D30     |       |          |
| CHKD                  |  | UNIT: mm/in                                                                                 | DWG NO.:<br>X-X6511WV-07H-C60D30    |       |          |
| APPD                  |  | SIZE: A4                                                                                    |                                     |       |          |
| PRECISION CO.,LIMITED |  |                                                                                             | WEIGHT                              | SHEET | REVISION |
|                       |  |                                                                                             |                                     | 1/1   | A0       |