



环境测试后: ≤ 20 兆欧



	X9357HF-2x03-N2BK	Nylon 66 94V-2 Black	X9357TM	X9357W Or 9357H	Without Ears
	X9357HF-2x03G-N2	Nylon 66 94V-2			With Ears
	X9357HF-2x03I-N2	Nylon 66 94V-2			Without Ears
	X9357HF-2x03G-N0	Nylon 66 94V-0			With Ears
	X9357HF-2x03I-N0	Nylon 66 94V-0			Without Ears
	PART NO	Material	Suitable XKB Terminal	Suitable XKB Housing	Note

XKB	DSND		DATE		SCALE: N/A	MODEL TYPE:
±5°	DWN		DATE		VIEW: 	2.40mm Crimp Style Connectors
±0.2						PART NO.:
±0.3	CHKD		DATE		UNIT: mm/in	X9357HF-2x03G-N2
±0.4	APPD		DATE		SIZE: A4	DWG NO.:
±0.5						X-9357HF-2x03G-N2

				XKB	ANGLAR	$\pm 5^\circ$
Δx					$L \leq 4$	± 0.2
Δx					$4 < L \leq 16$	± 0.3
Δx					$16 < L \leq 63$	± 0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	$L > 63$	± 0.5

XKB INDUSTRIAL PRECISION CO.,LIMITED

WEIGHT	SHEET	REVISION
1.0g	1/1	A0