




■ Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -40°C~+85°C
- Insulation resistance: $\geq 1000M\Omega$
- Contact resistance: $\leq 10m\Omega$
- After environmental testing : $\leq 20m\Omega$



X8821 W V-10 K- N0 SN
① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② Category : W-WAFER
- ③ Wedding Board Angle : V-Stright 180°
- ④ Row No.-Pin No.: XX-02P~20P
- ⑤ Plug the Pin\$ Special No.:K-KINK
- ⑥ Material : N0-PA66;46-PA46 94V-0
- ⑦ Plating Category: Sn-Bright Tin Plating



Recommended P.C.B Layout
General Tolerance ± 0.05

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	2,50	7,50	12	27,50	32,50
03	5,00	10,00	13	30,00	35,00
04	7,50	12,50	14	32,50	37,50
05	10,00	15,00	15	35,00	40,00
06	12,50	17,50	16	37,50	42,50
07	15,00	20,00	17	40,00	45,00
08	17,50	22,50	18	42,50	47,50
09	20,00	25,00	19	45,00	50,00
10	22,50	27,50	20	47,50	52,50
11	25,00	30,00			

X8821WV-10K-46SN	PA46 UL 94V-0	Brass	Tin-Plated	X8821H
X8821WV-10-N0SN	Nylon 66 UL 94V-0			
PART N0	Material	Material(pin)	Finish(pin)	Suitable XKB Housing

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.5mm Crimp Style Connectors				
					ANGLAR	±5°	DWN		DATE		VIEW: 	PART NO.: X8821WV-10K-N0SN				
Δx					L ≤ 4	±0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X8821WV-10K-N0SN				
Δx					4<L ≤ 16	±0.3										
Δx					16<L ≤ 63	±0.4										
MARK	DESCRIPTION			DATE	REVISED	APPROVED	APPD		DATE		SIZE: A4					
REVISIONS							XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT			SHEET	REVISION
UNSPECIFIED TOLERANCES															1/1	
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn																