



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.22	阿树





Specifications:
规格:
Current rating:3A AC/DC
额定电流: 3A AC/DC
Voltage rating:250V AC
额定电压: 250V AC
Withstanding voltage:500V AC/MIN
耐受电压: ≥500V AC/分钟
Temperature range:-55℃~+105℃
温度范围: -55℃~+105℃
Insulation resistance:1000MΩMIN
绝缘电阻: ≥1000MΩ
Contact resistance:30mΩMAN
接触电阻: ≤30mΩ
Material And FINISHED:
材料和成本:
INSULATOR:PBT UL 94V-0
绝缘体: PBT UL 94V-0
SHELL: SPCC-SD Plated Ni / Au / Sn
外壳: 铁合金 镀镍/金/锡
CONTACT MATERIAL:COPPER ALLOY
触点材料: 铜合金





PART NO.:

X03 37 W I Z B Z
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series NO.
②Row No.Pin No.XX-09;15;25;37
③Welding Board Angle :W-Male
④T: Tradutional
⑤Planting Category: 1:1U' 2:2U' 3:3U' 4:5U' 5:15U' 6:30U' 7:AuSn
⑥Color:B:Black W:White BL:Blue Y:Yellow G:Green R:Red
⑦1:TYPE-1; 2:TYPE-2; 3:TYPE-3; 4:TYPE-4; 6:TYPE-6

NO.OF CONTACT	A	B	C
09	30.81	24.99	16.92
15	39.14	33.32	25.25
25	53.04	47.04	38.96
37	69.32	63.50	55.42



铆合方式		TYPE-1:铆合	TYPE-6:直铆锁	TYPE-3:叉锁	TYPE-2:铆合锁螺丝
图式					
	DESIGN	阿树	VIEW: 	MODEL TYPE: D-SUB	
	CHECKED		UNIT: mm/in	PART NO.: X0337WT7B2	
	APPROVED		SIZE: A4	DWG NO.: X-X0337WT7B2	
	PRECISION CO.,LIMITED			SCALE N/A	PAGE 1/1

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCE	

XKB 星树
Connection

XKB INDUSTRIAL PRECISION CO.,LIMITED