







R1



R2



PCB LAYOUT (R1)



PCB LAYOUT (R2)

Specifications:
规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:1A AC/DC
额定电流: 1A AC/DC
Withstanding voltage:300V AC/minute
耐受电压: 300V AC/分钟
Temperature range:-40℃-+105℃
温度范围: -40℃-+105℃
Insulation resistance:≥500MΩ
绝缘电阻: ≥500MΩ
Contact resistance:≤20mΩ
接触电阻: ≤20mΩ
Material:PA6T UL94V-0
材质: PA6T UL94V-0
Plating Category:1U"Gold
镀层: 1U"Gold
Reflow soldering temperature:260±5℃, 10S
回流焊温度: 260±5℃, 10S

X1311 F V S - 12 - C43 D35 R1
① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- 1.Series No
- 2.Category:F-Female
- 3.Welding Board Angle:V-Stright 180°
- 4.Welding Way:S-SMT
- 5.Row No.Pin No:XX-01~40Pin
- 6.Plastic Height:C=4.3mm
- 7.Pin pitch:D=3.5mm
- 8.Type:R1 ; R2

X1311FVS-12-C43D35R1	PA6T	Brass	X1311W
PART N0	Material	Material(Pin)	Suitable XKB Wafer

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5
REVISIONS					UNSPECIFIED TOLERANCES	
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE: 1.27mm BTB Connector		
DWN		VIEW: 	PART NO.: X1311FVS-12-C43D35R1		
CHKD		UNIT: mm/in	DWG NO.: X-X1311FVS-12-C43D35R1		
APPD		SIZE: A4			
PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0