


Specifications:  
规格:  
Voltage rating:250V AC/DC  
额定电压: 250V AC/DC  
Current rating:1A AC/DC  
额定电流: 1A AC/DC  
Withstanding voltage:500V AC/minute  
耐受电压: 500V AC/分钟  
Temperature range:-40℃--+105℃  
温度范围: -40℃--+105℃  
Insulation resistance: 1000MΩ min  
绝缘电阻: 1000MΩ Min  
Contact resistance:20mΩ Max  
接触电阻: 20mΩ Max

X2001 W V - 2x04 A - 6T V01  
① ② ③ ④ ⑤ ⑥ ⑦  
1.Series No  
2.Category:W-Wafer  
3.Welding Board Angle:V-Stright 180°  
4.Row No.Pin No: 2xXX-2x03-2x30P  
5.Category:A-No gap  
6.Material:6T-Nylon 6T UL94V-0  
7.Plating:V01-Gold Flash

| Poles | Dimensions |       | Poles | Dimensions |       |
|-------|------------|-------|-------|------------|-------|
|       | A          | B     |       | A          | B     |
| 2x03  | 4.00       | 13.30 | 2x12  | 22.00      | 31.30 |
| 2x04  | 6.00       | 15.30 | 2x13  | 24.00      | 33.30 |
| 2x05  | 8.00       | 17.30 | 2x15  | 28.00      | 37.30 |
| 2x06  | 10.00      | 19.30 | 2x17  | 32.00      | 41.30 |
| 2x07  | 12.00      | 21.30 | 2x18  | 34.00      | 43.30 |
| 2x08  | 14.00      | 23.30 | 2x20  | 38.00      | 47.30 |
| 2x09  | 16.00      | 25.30 | 2x22  | 42.00      | 51.30 |
| 2x10  | 18.00      | 27.30 | 2x25  | 48.00      | 57.30 |
| 2x11  | 20.00      | 29.30 | 2x30  | 58.00      | 67.30 |

|                     |          |               |                  |
|---------------------|----------|---------------|------------------|
| X2001WV-2x04A-6TV01 | Nylon 6T | Brass         | X2001HA-2x04     |
|                     |          |               | X2001HA2-2x04    |
| PART N0             | Material | Material(Pin) | Suitable XKB IDC |

|                                      |  |                                                                                             |                                     |       |          |
|--------------------------------------|--|---------------------------------------------------------------------------------------------|-------------------------------------|-------|----------|
| DSND                                 |  | SCALE: N/A                                                                                  | MODEL TYPE:<br>2.0mm Jane cattle 简牛 |       |          |
| DWN                                  |  | VIEW:  | PART NO.:<br>X2001WV-2x04A-6TV01    |       |          |
| CHKD                                 |  | UNIT: mm/in                                                                                 | DWG NO.:<br>X-X2001WV-2x04A-6TV01   |       |          |
| APPD                                 |  | SIZE: A4                                                                                    | WEIGHT                              | SHEET | REVISION |
| XKB INDUSTRIAL PRECISION CO.,LIMITED |  |                                                                                             |                                     | 1/1   | A0       |



P . C . B LAYOUT

|                                               |  |  |  |  |                        |      |
|-----------------------------------------------|--|--|--|--|------------------------|------|
|                                               |  |  |  |  | ANGLAR                 | ±5°  |
| ΔX                                            |  |  |  |  | L≤ 4                   | ±0.2 |
| ΔX                                            |  |  |  |  | 4<L≤ 16                | ±0.3 |
| ΔX                                            |  |  |  |  | 16<L≤ 63               | ±0.4 |
| MARK                                          |  |  |  |  | L> 63                  | ±0.5 |
| REVISIONS                                     |  |  |  |  | UNSPECIFIED TOLERANCES |      |
| www.helloxkb.com www.helloxkb.cn www.xk-dg.cn |  |  |  |  |                        |      |