






REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.1.2	阿树



SECTION:A-A
SCALE:1:1



Current rating:5A AC/DC
额定电流:5A AC/DC
Temperature range:-40℃~+125℃
温度范围: -40℃~+125℃



PART NO.:

K 967280 W R-42-PT SN
① ② ③ ④ ⑤ ⑥ ⑦

- ①K:XKBTEK-Car Connector
- ②XKB Series No
- ③Category:W-Wafer
- ④Welding Board Rangle:R-Stright 90°
- ⑤Row No.Pin No:XX-42 Pin
- ⑥Material:PT-PBT
- ⑦Palting:SN-Plated Tin



PCB LAYOUT

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树	VIEW:		MODEL TYPE: 5.0mm Automobile connector		
CHECKED		UNIT: mm/in		PART NO.: K967280WR-42-PTSN		
APPROVED		SIZE: A4		DWG NO.: X-K967280WR-42-PTSN		
PRECISION CO.,LIMITED				SCALE	PAGE	REVISION
				N/A	1/1	A1