



Specifications:
规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating: 3A AC/DC
额定电流: 3A AC/DC
Withstanding voltage: 1500V AC/minute
耐压电压: 1500V AC/minute
Temperature range:-25℃～+85℃
温度范围: -25℃～+85℃
Insulation resistance:≥500MΩ
绝缘电阻: ≥500MΩ
Contact resistance: ≤10Ω
接触电阻: ≤10Ω
After environmental testing:≤20mΩ
环境测试后: ≤20mΩ

Poles	Dimensions(mm)		
	A	B	C
2	7.50	5.8	2.50
3	10.00	8.3	5.00
4	12.50	10.8	7.50
5	15.00	13.3	10.00
6	17.50	15.8	12.50
7	20.00	18.3	15.00
8	22.50	20.8	17.50
9	25.00	23.3	20.00
10	27.00	25.80	22.50
11	12.50	28.30	25.00
12	15.00	30.80	27.50
13	17.50	33.30	30.00
14	20.00	35.80	32.50
15	22.50	38.30	35.00

X2508WV-12-N0SN	Nylon 66 UL 94V-0	Brass	Tin Plated	X2508H
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Housing

							DSND		DATE		SCALE: N/A	MODEL TYPE: 2.50 mm Crimp Style Connectors		
ΔX					ANGULAR	$\pm 5^\circ$	DWN		DATE		VIEW: 	PART NO.: X2508WV-12-N0SN		
ΔX					$L \leq 4$	± 0.2	CHKD		DATE		UNIT: mm/in	DWG NO.: X-X2508WV-12-N0SN		
ΔX					$4 < L \leq 16$	± 0.3								
ΔX					$16 < L \leq 63$	± 0.4	APPD		DATE		SIZE: A4			
MARK	DESCRIPTION			DATE	REVISED	APPROVED								
REVISIONS							UNSPECIFIED TOLERANCES					XKB INDUSTRIAL PRECISION CO.,LIMITED		
www.xk-dq.cn www.helloxkb.com www.helloxkb.cn												WEIGHT	SHEET	REVISION
												1.0a	1/1	A0