






XKB




X9357 W R X-2x06S-N2SN

- 01 Series No.
02 Category:W-wafer
03 Welding Board Angle:R-90°
04 Welding Way: Blank-DIP;
05 Row No.-Pin No.: 2*XX-Double row
06 Special NO.
s-With positioning column F-halogen free
07 Material:NO-PA6694V-0:N2-PA6694V-2
LP-LCP 94V-0
08 Planting Category: SN-Bright tin plating 70u"
09 Color: Blank-natural color
BK-BLACKBL-BLUE RE-RED

Specifications:
规格: **XKB**
Voltage rating:600V AC/DC
额定电压: 600V AC/DC
Current rating:9A AC/DC
额定电流: 9A AC/DC
Withstanding voltage:1500V AC/minute
耐受电压: 1500V AC/分钟
Temperature range:-25℃-+85℃
温度范围: -25℃-+85℃
Insulation resistance:≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance:≤10mΩ
接触电阻: ≤30mΩ
After environmental test:≤20mΩ
环境测试后: ≤20兆欧

Poles	Dimensions(mm)	
	A	B
2*01	---	5.40
2*02	4.20	9.60
2*03	8.40	13.80
2*04	12.60	18.00
2*05	16.80	22.20
2*06	21.00	26.40
2*07	25.20	30.60
2*08	29.40	34.80
2*09	33.60	39.00
2*10	37.80	43.20
2*11	42.00	47.40
2*12	46.20	51.60



△	X9357WR-2x06S-LPSN	LCP UL 94V-0	Brass	Tin- Plated	X9357H
	X9357WR-2x06SF-NOSNBK	Nylon 66 UL 94V-0 Halogen Free			
	X9357WR-2x06S-N0SN	Nylon 66 UL 94V-0			
	X9357WR-2x06S-N2SN	Nylon 66 UL 94V-2			
PART NO		Material	Materral(Pin)	Finlsh(Pin)	Suitable XKB Housing

XKB						DSND		DATE		SCALE: N/A	MODEL TYPE: 2.40mm Crimp Style Connectors
ΔX						DWN		DATE		VIEW:	PART NO.: X9357WR-2x06S-N2SN
ΔX						CHKD		DATE		UNIT: mm/in	DWG NO.: X-X9357WR-2x06S-N2SN
ΔX						APPD		DATE		SIZE: A4	WEIGHT 1.0g
MARK						XKB INDUSTRIAL PRECISION CO.,LIMITED					SHEET 1/1
REVISIONS						UNSPECIFIED TOLERANCES					REVISION A0
www.helloxkb.com											