

1

2

3



4

A




B

C

D



PCB.WELDING DRAWING



CIRCUIT DIAGRAM

REVISIONS

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.05.26	阿树

Code-x	H
A	4.30
B	4.50
C	5.00
D	5.50
E	6.00
F	6.50
G	7.00
H	7.50
I	8.00
J	8.50
K	9.00

SPECIFICATION

Contact Rating: 50mA,12V DC
Contact Resistance: 100mΩ max
Insulation Resistance: 100MΩ min.500V DC
Dielectric Strength: 250V AC/1minute
Travel: 0.30mm
Operating Temp: -25℃~+80℃
Storage Temp: -30℃~+80℃

PAPT NO	TC-FS66D-B-K
Operating Force	A:100gf B:160gf C:260gf
Height	Code-X

⑤	Terminal	4	Brass (0.30t)	Plating silvering
④	Contact	1	F.ag/SUS	Natural
③	Base	1	PPA	
②	Cover	1	PPA	
①	Keystake	1	PPA	
ITEM	PAPT NAMF	QTY	MATERIAL	FINISHING

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	TACT SWITCH
APPROVED		SIZE: A4	PART NO.: TC-FS66D-B-K
			DWG NO.: TC-FS66D-B-K
SCALE	N/A	PAGE	1/2
REVISION	A1		

1

2

3

4



A

B



C

D


Code-x	H
L	9.50
M	10.00
N	10.50
O	11.00
P	11.50
Q	12.00
R	12.50
S	13.00
T	13.50
U	14.00
V	15.00
W	15.50
X	16.00
Y	16.50
Z	17.00
18	18.00
19	19.00



SPECIFICATION
 Contact Rating: 50mA, 12V DC
 Contact Resistance: 100mΩ max
 Insulation Resistance: 100MΩ min. 500V DC
 Dielectric Strength: 250V AC/1minute
 Travel: 0.30mm
 Operating Temp: -25℃~+80℃
 Storage Temp: -30℃~+80℃



SCHEMATIC



P.C.B LAYOUT

PAPT NO	TC-FS66D-B-K
Operating Force	A:100gf B:160gf C:260g
Height	Code-X

⑤	Terminal	4	Brass (0.30t)	Plating silvering	
④	Contact	1	F.ag/SUS	Natural	
③	Base	1	PPA		
②	Cover	1	PPA		
①	Keystake	1	PPA		
ITEM	PAPT	NAMF	QTY	MATERIAL	FINISHING

AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED	TOLERAUCES

XKLB 星城
Connection

DESIGN	阿树	VIEW: 	MODEL TYPE: TACT SWITCH		
CHECKED		UNIT: mm/in	PART NO.: TC-FS66D-B-K		
APPROVED		SIZE: A4	DWG NO.: TC-FS66D-B-K		
PRECISION CO., LIMITED			SCALE	PAGE	REVISION
			N/A	2/2	A1