

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.2.27	阿树

A

B

C





D

A

B

C

D



Specifications:
规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:1A AC/DC
额定电流: 1A AC/DC
Withstanding voltage:300V AC/minute
耐受电压: 300V AC/分钟
Temperature range:-40℃-+105℃
温度范围: -40℃-+105℃
Insulation resistance:≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance:≤20mΩ
接触电阻: ≤20mΩ
Material:PA6T UL94V-0
材质: PA6T UL94V-0
Plating Category:1U"Gold
镀层: 1U"Gold
Wave soldering temperature:255±5℃, 10S
波峰焊温度: 255±5℃, 10S

PART NO.:
X1311 W R-02 J-C40 D24
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
- ②Category:W-Wafer
- ③Welding Board Angle:R-Stright 90°
- ④Row No -Pin No:XX Pin
- ⑤Plastic height:J=1.0mm
- ⑥Pin length: C=4.0mm
- ⑦Pin Length:D=2.4mm

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN
CHECKED
APPROVED

X1311WR-02J-C40D24	PA6T	Brass	X1311F
PART NO	Material	Material(Pin)	Suitable XKB Female
阿树	VIEW:	MODEL TYPE: 1.27mm BTB Connector	
	UNIT: mm/in	PART NO.: X1311WR-02J-C40D24	
	SIZE: A4	DWG NO.: X-X1311WR-02J-C40D24	
		SCALE	PAGE
		N/A	1/1
		REVISION	A1