

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.07.30	阿树




Specifications:
规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:1A AC/DC
额定电流: 1A AC/DC
Withstanding voltage:300V AC/minute
耐受电压: 300V AC/分钟
Temperature range:-40℃-+105℃
温度范围: -40℃-+105℃
Insulation resistance:≥500MΩ
绝缘电阻: ≥500MΩ
Contact resistance:≤20mΩ
接触电阻: ≤20mΩ
Material:PA6T UL94V-0
材质: PA6T UL94V-0
Plating Category:1U"Gold
镀层: 1U"Gold
Reflow soldring temperature:255±5℃, 10S
回流焊温度: 255±5℃, 10S

PART NO.:

X1321 W V-2x35 J-C30 D23
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Category:W-Wafer
③Welding Board Angle:V-Stright 180°
④Row No.Pin No:2xXX-2x01~2x40P
⑤Plastic Height:J=1.0mm
⑥Pin Length:C=3.0mm
⑦Pin Length:D=2.3mm

X1321WV-2x35J-C30D23	PA6T	Brass	X1321F
PART NO	Material	Material(Pin)	Suitable XKB Female
DESIGN	阿树	VIEW: 	MODEL TYPE: 1.27mm BTB Connector
CHECKED		UNIT: mm/in	PART NO.: X1321WV-2x35J-C30D23
APPROVED		SIZE: A4	DWG NO.: X-X1321WV-2x35J-C30D23
SCALE			PAGE
N/A			1/1
REVISION			A1



P.C.B LAYOUT

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED