




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.19	桑葚
A1	N/A		产品尺寸变更, 图面升级整理图面	2025.09.15	阿树



Specifications(规格):
1.Voltage rating(额定电压):250V AC DC
2.Current rating(额定电流):3.0A AC/DC
3.Withstanding voltage(耐压值):≥1500V AC/minute
4.Insulation resistance(绝缘电阻):800MΩ Min
5.Contact resistance(接触电阻):25mΩ Max
6.Temperature range(使用温度):-40℃~+125℃

PART NO.:
X2006 H-2x17-N0 HF
① ② ③ ④ ⑤

- ①Series No
②Category:H-HSG
③Row No.Pin No:2xXX-2x02~2x32Pin
④Material:NO-PA66 94V-0
⑤Plug the Pin&special No:
HF-Halogen Free



8P~14P Without Guide buulge
16P~40P With Guide buulge
Scale:1/0.8

poles	Dimensions(mm)			poles	Dimensions(mm)		
	A	B	C		A	B	C
2x04	6.00	10.00	8.65	2x13	24.00	28.00	26.65
2x05	8.00	12.00	10.65	2x14	26.00	30.00	28.65
2x06	10.00	14.00	12.65	2x15	28.00	32.00	30.65
2x07	12.00	16.00	14.65	2x16	30.00	34.00	32.65
2x08	14.00	18.00	16.65	2x17	32.00	36.00	34.65
2x09	16.00	20.00	18.65	2x18	34.00	38.00	36.65
2x10	18.00	22.00	20.65	2x19	36.00	40.00	38.65
2x11	20.00	24.00	22.65	2x20	38.00	42.00	40.65
2x12	22.00	26.00	24.65				

X2006H-2x17-N0HF	PA66 94V-0	X2006W	X2006T
PART NO.	MATERIAL	Suitable XKB Wafer	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuces	



DESIGN	阿树	VIEW:	MODEL TYPE: 2.0mm Crimp Style Housing
CHECKED		UNIT: mm/in	PART NO.: X2006H-2x17-N0HF
APPROVED		SIZE: A4	DWG NO.: X-X2006H-2x17-N0HF

SCALE	PAGE	REVISION
N/A	1/1	A1