




REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.10.17	阿树

A





SCHEMATIC



PCB LAYOUT
BOTTOM VIEW

B



SS23D06L6

L(mm)
2~10

C

D

RATING	0.3A 50V DC
CIRCUIT	2P3T
CONTACT RESISTANCE	100MΩ MAX
TRAVEL	2MM
OPERATING FORCE	250±100gf
OPERATING LIFE	10000

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAuCES	



DESIGN	阿树
CHECKED	
APPROVED	

VIEW:	
UNIT:	mm/in
SIZE:	A4

MODEL TYPE:	SLIDE SWITCH
PART NO.:	SS23D06L6
DWG NO.:	

SCALE	PAGE	REVISION
N/A	1/1	A1