


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.10.23	阿树

NOTES:
SPECIFICATION:
1.CURRENT RATING: 3.0A MAX
2.VOLTAGE: 100 VAC
3. TEMPERATURE RANGE: -30 ~85
4.CONTACT RESISTANCE: 40 MILLIONHM MAX
5.INSULATION RESISTANCE: 100 MEGOHMS MIN
6.INSERTION FORCE: 5N~20N
7.UNMATING FORCE: 8N~20N
8.DURABILITY: 10.000 CYCLES
9.WATER PROOFNESS:THISPRODUCTIS BASED ON IPX7



U262-061N-4BF712

- 1:0.8u"
2:5u"
3:10u"
- W:WHITE
B:BLACK
- 1:PBT
2:PA6T
3:PA9T
4:LCP

A5	CC1	B12	GND
A9	VBUS	B9	VBUS
A12	GND	B5	CC2
PIN	SIGNAL NAME	PIN	SIGNAL NAME

5	Shell	Stainless Steel	NI Plated	1PCS
4	Shielding Plate	Stainless Steel	NI Plated	1PCS
3	Contact	Copper Alloy	TIN/Au/NI Plated	1SET
2	Shell Housing	High Temperature Plastic	BLACK	1PCS
1	Housing	High emperature Plastic	BLACK	1PCS
NO.	DESCRIPTION	MATERIAL	REMARKS	QTY

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	阿树	VIEW:	MODEL TYPE: USB TYPE C SMT-06PIN PLUG
CHECKED		UNIT: mm/in	PART NO.: U262-061N-4BF712
APPROVED		SIZE: A4	DWG NO.: X-U262-061N-4BF712
SCALE	PAGE	REVISION	
N/A	1/1	A1	