


REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A1	N/A		图面升级整理图面	2025.06.16	阿树
A2	ECN-P-2026040101	A2 X1	产品外观, 尺寸及材质变更	2026.04.01	阿树



- Specifications (规格):
- 1.Voltage rating (额定电压):DC 12V
 - 2.Current rating (额定电流):0.5A AC/DC
 - 3.Withstanding voltage (耐压值):≥100V AC/minute
 - 4.Insulation resistance (绝缘电阻):≥100MΩ Min
 - 5.Contact resistance (接触电阻):≤20mΩ Max
 - 6.Mating cycles (使用寿命): 10,000 cycles Min
 - 7.Operating Force (操作力度):200±100gf
 - 8.Temperature range (使用温度):-10℃~+60℃

PAPT NO	L	foot
SK-3245S-L1-X	L1:2.00	A B
SK-3245S-L2-X	L2:2.50	A B
SK-3245S-L3-X	L3:3.00	A B
SK-3245S-L4-X	L4:4.00	A B

D	Cover	1	Sus	Natural
C	Contact spring	1	Phosphor branze	Ag Plated
B	Keystake	1	PPA/LCP	Black
A	Pedestal	1	PPA/LCP(Brass)	Ag Plated(Black)
ITEM	PAPT NAME	QTY	MATERIAL	FINISHING(COLOR)

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	SLIDE SWITCH
CHECKED		UNIT:	mm/in	PART NO.:	SK-3245S-L4-A
APPROVED		SIZE:	A4	DWG NO.:	

SCALE	PAGE	REVISION
N/A	1/1	A2

