



PCB LAYOUT

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-40℃~+105℃

温度范围: -40℃~+105℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

Material:PA6T UL94V-0

材质: PA6T UL94V-0

Plating Category:1U"Gold

镀层: 1U"Gold

Reflow soldering temperature:260±5℃, 10S

回流焊温度: 260±5℃, 10S

X6521	W	R	S	- 2x13	H	- C60	D75
①	②	③	④	⑤	⑥	⑦	⑧

1.Series No

2.Category:W-Wafer

3.Welding Board Angle:R-Stright 90°

4.Row No.Pin No:2xXX-2x01~2x40P

5.Plastic Height:H=2.5mm

6.Pin Length:C=6.0mm

7.Pin Length:D=7.5mm

X6521WRS-2x13H-C60D75	PA6T	Brass	X6521F
PART NO	Material	Material(Pin)	Suitable XKB Female

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGULAR ±5°
ΔX					L ≤ 4 ±0.2
ΔX					4 < L ≤ 16 ±0.3
ΔX					16 < L ≤ 63 ±0.4
MARK					L > 63 ±0.5
REVISIONS					UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn					

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND		SCALE: N/A	MODEL TYPE:
DWN		VIEW:	2.54mm BTB Connector
CHKD		UNIT: mm/in	PART NO.:
APPD		SIZE: A4	X6521WRS-2x13H-C60D75
			DWG NO.:
			X-X6521WRS-2x13H-C60D75
WEIGHT		SHEET	REVISION
		1/1	A0