

1

2

3

4

A

B

C






D

A

B

C

D



PCB LAYOUT

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	


规格 Specification:

- 1.额定值 Rating:3A 125/250VAC
- 2.接触电阻 Contact resistance:≤30 mΩ
- 3.绝缘电阻 Insulation resistance:≥100 MΩ(DC500V/Min)
- 4.电气寿命 Electronics life:>10000 cycles
- 5.操作力 Operation force:500±200gf
- 6.所有材料符合Rohs要求 All materials are Rohs compliant

PART NO.:

SS-X 03 23 P G-11 R 1 W B
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

- ① SS: XKB Vertical handle;
② Enclosure Material:
A-Metal case;
BLANK-Plastic case;
③ Current Rating: 03-03A;
④ Switch Circuit:23-2P3T;
⑤ P: Welding plates;
⑥ Handle Shape: G-Camber handle
⑦ Handle Height: 3~15mm;
⑧ Enclosure Shape:R-Locking rings enclosure;
⑨ Terminal specs:
1:TYPE-1; 2:TYPE-2;
3:TYPE-3; 4:TYPE-4; 5:TYPE-5;
⑩ Handle Colour:
B-Black; W-White; R-Red
⑪ Housing Colour:
B-Black; W-White; R-Red



ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DESIGN	桑 菴	VIEW:	MODEL TYPE: SLIDE SWITCH
CHECKED		UNIT: mm/in	PART NO.: SS-A0323PG-11R1WB
APPROVED		SIZE: A4	DWG NO.: X-SS-A0323PG-11R1WB
		SCALE	PAGE
		N/A	1/1
		REVISION	A0

1

2

3

4