

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.01.11	
A1	N/A			2025.12.26	

SPECIFICATION

- 1.VOLTAGE RATING 100V AC/DC.
- 2.CURRENT RATING 1A AC/DC.
- 3.WITHSTANDING VOLTAGE 500V AC/Minute.
- 4.TEMPERATURE RANGEL -40 ~+80 .
- 5.CONTACT RESISTANCE ≤40 mΩ Max.
- 6.INSULATION RESISTANCE ≥100 MΩ Min.
- 7.Use with:A1002H.

PART NO.:

X1008 I-P V01-A




Series Number.

Category: T-terminal

CMaterial:P-Phosphorous bronze

Plating style:V01-Gold Flash

Special NO:A-A Type



X1008T-PV01-A	Phosphor Bronze	Gold Flash	AWG#28~#32	0.75mm	X1008H
PART NO	Material	Finish	Wire Range	Insulation OD	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN
CHECKED
APPROVED

VIEW:
UNIT: mm/in
SIZE: A4

MODEL TYPE:
1.0mm Crimp Style Connector
PART NO.:
X1008T-PV01-A
DWG NO.: