


	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.12.23	阿树



■ SPECIFICATIONS





- Voltage rating:50V AC,DC
- Current rating:1A,AC,DC
- Withstanding Voltage:500V AC/minute
- Insulation resistance:100MΩ min
- Temperature range:-45°C+95°C
- Contact resistance:20mΩ max

PART NO.:

X1010 W V S-02-LP SN
① ② ③ ④ ⑤ ⑥ ⑦

- ①Series No
②Category:W-Wafer
③Welding Board Angle:V-Stright 180°
④Welding Way: S-SMT
⑤Row No.Pin No:XX-02~15Pin
⑥Material:LP-LCP UL94V-0
⑦Planting: SN-Tin-Plated
V01-Gold Flsh

PART NO.	Dimensions (mm)	
	A	B
02	2.00	5.00
03	2.00	5.00
04	3.00	6.00
05	4.00	7.00
06	5.00	8.00
07	6.00	9.00
08	7.00	10.00
09	8.00	11.00
10	9.00	12.00
11	10.00	13.00
12	11.00	14.00
13	12.00	15.00
14	13.00	16.00
15	14.00	17.00



AuGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERAUCES	

XK13 星城 Connection

X1010WVS-02-LPSN	LCP	Brass	X1010H
PART NO	Material	Material(Pin)	Suitable XKE Housing

DESIGN	阿树	VIEW: 	MODEL TYPE: 1.0mm Crimp Style Housing
CHECKED		UNIT: mm/in	PART NO.: X1010WVS-02-LPSN
APPROVED		SIZE: A4	DWG NO.:

SCALE	PAGE	REVISION
N/A	1/1	A1