

1

2

3

4

A

B

C


D

A

B

C



D



REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2024.9.06	阿树

■ SPECIFICATIONS

- Voltage rating: 250V AC/DC
- Current rating: 3A AC/DC
- Withstanding Voltage: 1000V AC/minute
- Temperature range: -40°C ~ +125°C
- Insulation resistance: $\geq 500M\Omega$
- Contact resistance: $\leq 20m\Omega$





PART NO.:

X1511 H-03 L-N0
① ② ③ ④ ⑤

- ① Series No
② Category: H-HSG
③ Row No. Pin No: XX-02~15P
④ Special N0: L-With Lock
⑤ Material: N0-Nylon 66 UL94V-0

Poles	Dimensions (mm)		
	A	B	C
02	1.50	4.10	3.30
03	3.00	5.60	4.80
04	4.50	7.10	6.30
05	6.00	8.60	7.80
06	7.50	10.10	9.30
07	9.00	11.60	10.80
08	10.50	13.10	12.30
09	12.00	14.60	13.80
10	13.50	16.10	15.30
11	15.00	17.60	16.80
12	16.50	19.10	18.30
13	18.00	20.60	19.80
14	19.50	22.10	21.30
15	21.00	23.60	22.80



AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	阿树	VIEW:	MODEL TYPE: 1.50mm Crimp Style Connectors
CHECKED		UNIT: mm/in	PART NO.: X1511H-03L-N0
APPROVED		SIZE: A4	DWG NO.: X-X1511H-03L-N0

1

2

3

4