




Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:600V AC/minute

耐受电压:600V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

After environmental testing:≤30mΩ

环境测试后: ≤30兆欧

Operating Temperature:-40℃ to +105℃

工作温度: -40℃至 +105℃

X9555WRX-2x05A-PTV01

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

1.Series No

2.Category:W-WAFER

3.Welding Board Angle:R-Right Angle 90°

4.Welding Way:Blank-DIP

5.Row No-Pin No:2xXX-2x06P-2x64P

6.Plug the Pin&Special N0:A-Ejector Header

7.Material:PT-PBT 94V-0

8.Plating Category:V01-All Gold Flash

9.Color:Blank-Natural Color

poles	Dimensions(mm)		poles	Dimensions(mm)	
	A	B		A	B
2x03	5.08	26.82	2x13	30.48	52.22
2x04	7.60	29.36	2x15	35.56	57.30
2x05	10.16	31.90	2x17	40.64	62.38
2x07	15.24	36.98	2x20	48.26	70.00
2x08	17.78	39.52	2x25	60.96	82.70
2x10	22.86	44.60	2x30	73.66	95.40
2x12	27.94	49.68	2x32	78.74	100.48

X9555WR-2x05A-PTV01	PBT UL 94V-0	Brass	Gold-Flash	X9555H
PART NO	Material	Material(pin)	Finish(Pin)	Suitable XKB Housing

						DSND		DATE		SCALE: N/A	MODEL TYPE:
						units:	mm	DWN		VIEW:	2.54mm Crimp Style Connectors
						tolerance:		CHKD		UNIT: mm/in	PART NO.:
						X.X	±0.2mm				X9555WR-2x05A-PTV01
						X.XX	±0.1mm	APPD		SIZE: A4	DWG NO.:
						X.XXX	±0.05mm				X-X9555WR-2x05A-PTV01
MARK	DESCRIPTION	DATE	REVISED	APPROVED		UNSPECIFIED TOLERANCES		XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT
REVISIONS											SHEET
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn											1/1
											REVISION
											A0