

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2025.09.05	
/	N/A		/	/	/

A

A

B


B

C

C

D

D



Specifications:

Voltage rating:250V AC/DC
250V AC/DC
Current rating:1A AC/DC
1A AC/DC
Withstanding voltage:1500V AC/minute
1500V AC/
Temperature range:-40 -+125
-40 -+125
Insulation resistance:≥1000MΩ
≥1000MΩ
Contact resistance:≤20mΩ MAX
≤20mΩ MAX

PART NO.:

X9555 I-P SN-B1

Series Number.
Category: T-terminal
Material:P-Phosphor Bronze
Plating:SN-Tin Plating
Other Types B1-Loose Type

X9555T-PSN-B1	Phosphor Bronze	AWG#22-28	Tin-Plated	X9555H-E(2x14~2x32 X9555H-E2(2x14~2x32 X9555H-E3(2x14~2x32
PART NO	Material	Wire Range	Finish(Pin and Solder tab)	Suitable XKB Housing

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



DESIGN	
CHECKED	
APPROVED	

VIEW:
UNIT: mm/in
SIZE: A4

MODEL TYPE: 2.54mm Crimp Style Connector
PART NO.: X9555T-PSN-B1
DWG NO.: