

1

2



3

4

REVISIONS					
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	/	/
A1	N/A		图面升级整理图面	2025.1.3	阿树


A

A



B

B



Current rating:3A AC/DC
额定电流: 3A AC/DC
Temperature range:-40℃-+125℃
温度范围: -40℃-+125℃



PART NO.:

K 137635 H M-2x12 B-N0
① ② ③ ④ ⑤ ⑥ ⑦

- ①K:XKBTEK-Car Connector
②XKB Series No
③Category:H-Housing
④Category:M-Male Housing
⑤Row No.Pin No:2x12 Pin
⑥Special No:B-Misaligned foot
⑦Material:N0-PA66 UL 94V-0

C

C



D

D

K137635HM-2xXXB-N0	PA66	Gray	K137635TF-B
PART NO	Material	Color	Suitable XKB Terminal

AuGLAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERAUCES	



DESIGN	阿树	VIEW:		MODEL TYPE:	2.2mm Automobile connector
CHECKED		UNIT:	mm/in	PART NO.:	K137635HM-2x12B-N0
APPROVED		SIZE:	A4	DWG NO.:	

1

2

3

4