





1

2

3

4



产品字码标识

ANGULAR	±5°
X.	±0.40
X.x	±0.30
X.xx	±0.20
X.xxx	±0.15
UNSPECIFIED TOLERANCES	



XKB INDUSTRIAL PRECISION CO.,LIMITED

REVISIONS

REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE	2024.05.09	



规格 Specification:

- 额定值 Rating: 3A 125/250VAC
- 接触电阻 Contact resistance: ≤30 mΩ
- 绝缘电阻 Insulation resistance: ≥100 MΩ (DC500V/Min)
- 电气寿命 Electronics life: >10000 cycles
- 操作力 Operation force: 400±150gf
- 所有材料符合RoHS要求 All materials are RoHS compliant

PART NO.:

SS-X 03 25 P G-15 N 3 W W
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

- ① SS: XKB Vertical handle;
- ② Enclosure Material:
 - A-Metal case;
 - BLANK-Plastic case;
- ③ Current Rating: 03-03A;
- ④ Switch Circuit: 25-2P5T;
- ⑤ P: Welding plates;
- ⑥ Handle Shape: G-Camber handle;
- ⑦ Handle Height: 3~15mm;
- ⑧ Enclosure Shape: N-Square enclosure;
- ⑨ Terminal specs:
 - 1: TYPE-1; 2: TYPE-2;
 - 3: TYPE-3; 4: TYPE-4; 5: TYPE-5;
- ⑩ Handle Colour:
 - B-Black; W-White; R-Red
- ⑪ Housing Colour:
 - B-Black; W-White; R-Red



DESIGN	桑 荳	VIEW:	MODEL TYPE: SLIDE SWITCH
CHECKED		UNIT: mm/in	PART NO.: SS-0325PG-15N3WW
APPROVED		SIZE: A4	DWG NO.: X-SS-0325PG-15N3WW
			SCALE: N/A
			PAGE: 1/1
			REVISION: A0

1

2

3

4