






P . C . B LAYOUT

Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range:-40℃-+85℃

温度范围: -40℃-+85℃

Insulation resistance:1000MΩ min

绝缘电阻: 1000MΩ Min

Contact resistance:20mΩ Max

接触电阻: 20mΩ Max

X8821 W R-15 S- N0 SN
① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:W-Wafer
- 3.Welding Board Angle:R-Stright 90°
- 4.Row No.Pin No:XX-02~20P
- 5.Special No:S-No Positioning
- 6.Material:N0-Nylon UL94V-0
- 7.Plating:SN-Tin Plated

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.50	7.50	6.00	10	22.50	27.50	26.00
03	5.00	10.00	8.50	11	25.00	30.00	28.50
04	7.50	12.50	11.00	12	27.50	32.50	31.00
05	10.00	15.00	13.50	13	30.00	35.00	33.50
06	12.50	17.50	16.00	14	32.50	37.50	36.00
07	15.00	20.00	18.50	15	35.00	40.00	38.50
08	17.50	22.50	21.00	-			
09	20.00	25.00	23.50	20	47.50	52.50	51.00

X8821WR-15S-N0SN	Nylon	Brass	X8821H
PART NO	Material	Material(Pin)	Suitable XKB Housing

DSND		SCALE: N/A	MODEL TYPE: 2.5mm Crimp Style Connector		
DWN		VIEW: 	PART NO.: X8821WR-15S-N0SN		
CHKD		UNIT: mm/in	DWG NO.: X-X8821WR-15S-N0SN		
APPD		SIZE: A4			
L PRECISION CO.,LIMITED			WEIGHT	SHEET	REVISION
				1/1	A0

					ANGLAR	±5°
ΔX					L≤ 4	±0.2
ΔX					4<L≤ 16	±0.3
ΔX					16<L≤ 63	±0.4
MARK					L> 63	±0.5
DESCRIPTION					DATE	REVISED
REVISIONS					APPROVED	UNSPECIFIED TOLERANCES
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn						

XKLB

XKB INDUSTRIAL PRECISION CO.,LIMITED