





	REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN
A0	N/A		INITIAL RELEASE		
A1	N/A		产品图面变更, 图面升级整理图面	2024.08.19	阿树



2x02P





2x03P~04P




2x05P~06F

■ SPECIFICATIONS


- Voltage rating:250V AC/DC
- Current rating:3A AC/DC
- Withstanding Voltage:800V AC/minute
- Temperature range:-45°C~+125°C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤20mΩ



2x07P以上



2x02P~03P



2x05P~07P

PART NO.:

X2015 H-2x04 - N0

① ② ③ ④

- 1.Series No
2.Category:H-HSG
3.Row No.Pin No:2xXX-02~20P
4.Material:N0-Nylon66 UL94V-0

Poles	Dimensions(mm)			
	A	B	C	D
2X02	2.00	4.90	4.90	3.90
2X03	4.00	6.90	6.90	3.90
2X04	6.00	8.90	8.90	3.90
2X05	8.00	12.00	10.40	5.90
2X06	10.00	14.00	12.40	5.90
2X07	12.00	16.00	14.40	5.90
2X08	14.00	18.00	16.40	10.90
2X09	16.00	20.00	18.40	10.90
2X10	18.00	22.00	20.40	10.90
2X11	20.00	24.00	22.40	10.90
2X12	22.00	26.00	24.40	10.90
2X13	24.00	28.00	26.40	10.90
2X14	26.00	30.00	28.40	10.90
2X15	28.00	32.00	30.40	10.90
2X16	30.00	34.00	32.40	10.90
2X17	32.00	36.00	34.40	10.90
2X18	34.00	38.00	36.40	10.90
2X19	36.00	40.00	38.40	10.90
2X20	38.00	42.00	40.40	10.90

X2015H-2x04-N0	Nylon66	X2015W	X2015T
PART NO	Material	Suitable XKB Wafer	Suitable XKB Terminal

ANGLAR	$\pm 5^\circ$
X.	± 0.40
X.x	± 0.30
X.xx	± 0.20
X.xxx	± 0.15
UNSPECIFIED TOLERANCES	

XK13 星城
Connection

DESIGN	阿树	VIEW:		MODEL TYPE: 2.00mm Crimp Style Connector
CHECKED		UNIT: mm/in		PART NO.: X2015H-2x04-N0
APPROVED		SIZE: A4		DWG NO.: X-X2015H-2x04-N0
DESIGN CO., LIMITED			SCALE	PAGE
			REVISION	

XKB INDUSTRIAL PRECISION CO.,LIMITED

