





PCB LAYOUT



R1 TYPE



R2 TYPE

Specifications:

规格:

Voltage rating: 250V AC/DC

额定电压: 250V AC/DC

Current rating: 3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage: 1000V AC/minute

耐受电压: 1000V AC/分钟

Temperature range: -40°C~+105°C

温度范围: -40°C~+105°C

Insulation resistance: ≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance: ≤20mΩ

接触电阻: ≤20mΩ

Material: PA6T UL94V-0

材质: PA6T UL94V-0

Plating Category: 1U"Gold

镀层: 1U"Gold

Wave soldering temperature: 255±5°C, 10S

波峰焊温度: 255±5°C, 10S

X6511	W	R	- 24	H -	C60	D30	R1
①	②	③	④	⑤	⑥	⑦	⑧

1.Series No

2.Category: W-Wafer

3.Welding Board Angle: R-Stright 90°

4.Row No.Pin No: XX-02~40P

5.Plastic Height: H=2.5mm

6.Pin Length: C=6.0mm

7.Pin Length: D=3.0mm

8.Type: X-R1 ; R2

X6511WR-24H-C60D30R1	PA6T	Brass	X6511F
PART NO	Material	Material(Pin)	Suitable XKB Female

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
ΔX					ANGULAR ±5°
ΔX					L ≤ 4 ±0.2
ΔX					4 < L ≤ 16 ±0.3
ΔX					16 < L ≤ 63 ±0.4
ΔX					L > 63 ±0.5
REVISIONS					
www.helloxkb.com	www.helloxkb.cn	www.xk-dg.cn			

XKB

XKB INDUSTRIAL PRECISION CO.,LIMITED

DSND	SCALE: N/A	MODEL TYPE:
DWN	VIEW:	2.54mm BTB Connector
CHKD	UNIT: mm/in	PART NO.:
APPD	SIZE: A4	X6511WR-24H-C60D30R1
		DWG NO.:
		X-X6511WR-24H-C60D30R1
	WEIGHT	SHEET
	1/1	REVISION
		A0